

[See all 1 Products in Family](#)

## UV Radiometer Unit



UV Radiometer Unit, #88-136

Stock **#88-136** CLEARANCE **1 In Stock**

MRP ₹1,23,192

Price inclusive of all taxes

**ADD TO CART**

Volume Pricing	
Qty 1+	₹1,23,192 each
Need More?	<a href="#">Request Quote</a>

**Note:** This item requires accessories for use | [Learn More](#)

### Product Downloads

#### General

3.5 digit LCD **Type of Display:**  
2.8 readings/sec **Conversion Rate:**

#### Physical & Mechanical Properties

0.3 **Weight (kg):**

157 x51 x91

**Dimensions (mm):**

± 2

**Accuracy (%):**

**Electrical**

**Intensity Range:**

Switchable:  
0 – 20 mW/cm<sup>2</sup>  
0 – 200 μW/cm<sup>2</sup>  
0 – 2000 μW/cm<sup>2</sup>

**Hardware & Interface Connectivity**

**Power Requirement:**

9 V Battery (not included)

**Regulatory Compliance**

**Certificate of Conformance:**

[View](#)

**Country of Origin:**

United States

**Imported By:**

Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Designed to Detect UV Wavelengths from 250 – 380nm
- NIST Certified Sensors
- 9V Battery Provides up to 120 Hours of Operation
- Requires One NIST Traceable Sensor for Operation

The NIST Certified UV Radiometer is ideal for inspecting ultraviolet light sources in a variety of quality control applications. The NIST Certified UV Radiometer is powered by a standard 9V battery for up to 120 hours of operation. Three NIST certified interchangeable sensors are available to detect a wide range of ultraviolet wavelengths from 250 – 380nm. The NIST Certified UV Radiometer's range switch allows the selection of three intensity ranges.

**Note:** The UV Radiometer Unit ([#88-136](#)) requires one NIST Traceable Sensor ([#88-137](#), [#88-138](#), or [#88-139](#)) for operation.

;