

[See all 12 Products in Family](#)

UV Solarization-Resistant Fiber Patch Cord, 200 μm Core, Stainless steel BX

See More by [Ocean Optics](#)



Stock #90-553 **NEW** 1 In Stock

MRP ₹34,515

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹34,515 each
Need More?	Request Quote

Product Downloads

General

QP200-2-SR-BX **Model Number:**

Physical & Mechanical Properties

2 **Length (m):**

200 **Core Diameter (μm):**

Stainless-steel BX **Jacket Material:**

Optical Properties

0.22 **Numerical Aperture NA:**

200 - 1100 **Wavelength Range (nm):**

Hardware & Interface Connectivity

SMA **Connector:**

Material Properties

Polyimide **Buffer Material:**

Regulatory Compliance

Compliant **RoHS 2015:**

View **Certificate of Conformance:**

Compliant **Reach 250:**

China **Country of Origin:**

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Connects Directly with Ocean Optics Spectrometers & Accessories
- Broad Wavelength Coverage: VIS-NIR, SR, and XSR Fibers Optimized for 180–2100 nm
- Solarization-Resistant Fibers Maintain Signal Accuracy Under Harsh UV
- Multiple Jacketing Choices for Durability and Tight Bend Radius Needs

Ocean Optics offers a complete line of premium optical fiber patch cords compatible with [Ocean Optics spectrometers](#) to suit a range of VIS-NIR and UV-NIR spectroscopy needs. Use them as illumination or read fibers to connect spectrometers, light sources, probes, or sampling accessories with maximum transmission efficiency and minimal signal loss. Choose standard visible-NIR assemblies for broadband applications or select solarization-resistant options to maintain signal fidelity when working with high UV power. Ocean Optics Spectrometer Patch Cords are available with a range of jacketing options designed to enhance durability and accommodate applications requiring a tight bend radius.

VIS-NIR Patch Cords (400–2100 nm): Best for routine broadband spectroscopy with minimal OH content, minimizing light absorption caused by hydroxyl ions (OH⁻), for efficient NIR transmission.

Solarization-Resistant Patch Cords (200–1100 nm): Ideal for UV-NIR work where standard silica fibers degrade under high UV exposure.

Extreme Solarization-Resistant Patch Cords (180–800 nm): Essential for deep-UV applications where the highest UV resistance is required.