

SWIR 1000nm Slip Mount Bandpass Filter



Slip Mount Machine Vision Filters

Stock **#70-544** **5 In Stock**

-

1

+

₹17,205

ADD TO CART

Volume Pricing	
Qty 1-9	₹17,205 each
Qty 10+	₹16,345 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

SWIR Bandpass Filter

Type:

Includes Locking Set Screws and Wrench

Note:

Physical & Mechanical Properties	
13.00	Clear Aperture CA (mm):
14.00	Inner Diameter (mm):
16.80	Outer Diameter (mm):
Mounted in Black Anodized Ring	Construction:
1.75	Substrate Thickness (mm):
Optical Properties	
1,000.00	Center Wavelength CWL (nm):
150.00	Full Width-Half Max FWHM (nm):
≥80	Minimum Transmission (%):
Hard Coated	Coating:
SVMR	Color:
930 - 1030	Transmission Wavelength (nm):
750 - 880 , 1200 - 1900	Blocking Wavelength Range (nm):
Threading & Mounting	
7.8	Mount Thickness (mm):
Regulatory Compliance	
View	Certificate of Conformance:
Compliant	Reach 242:

PRODUCT DETAILS

- Designed for Filter Threadless Imaging Lenses
- Available in UV, VIS, NIR, and SVMR Wavelengths
- ≥80% Transmission

Slip Mount Machine Vision Filters are ideal for use with varifocal lenses, wide-angle lenses, and lenses lacking filter threads. These filters are designed to fit securely over varifocal and wide angles lenses as they often do not come with filter threads due to the presence of a protruding convex lens element. Their low-profile and oversized diameter prevent wide-angle lens vignetting, and the inclusion of locking set screws and a wrench ensures secure attachment to the lens. Slip Mount Machine Vision Filters feature a 14mm inner diameter and are also compatible with M12 imaging lenses. These filters are designed with a Gaussian transmission curve and can achieve the output profile of common LED wavelengths when using a broadband light source.