

# Teledyne Dalsa Xtium2-CXP PX8 CoaXPress Frame Grabber

See More by [Teledyne DALSA](#)



Stock #91-739 **NEW** [CONTACT US](#)

MRP ₹96,748

**!** Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1+	₹96,748 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

**Model Number:**  
OR-A8X0-XPX10  
**Manufacturer:**  
Teledyne DALSA

### Sensor

**Image Buffer:**  
2GB  
**Pixel Depth:**  
Mono: 8, 10, 12, 14 and 16-bit; RGB: 8, 10 or 12-

## Hardware & Interface Connectivity

CoaXPress **Interface:**

PCIe Gen3 x8 slot **Computer Interface:**

1 Port (1 Camera) **Ports:**

## Regulatory Compliance

[Exempt](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

Canada **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- High Data Throughput with Reliable, Low-Latency Image Transfer
- Minimizes CPU Usage and Improves Processing Times
- High Performance for Camera Link®, Camera Link® HS, GigE, and CoaXPress® Interface Standards

Teledyne DALSA Frame Grabbers provide high-performance image acquisition solutions for demanding machine vision and industrial imaging applications. Designed to support a wide range of camera interface standards and data rates, these frame grabbers deliver reliable, high-bandwidth image transfer with low latency. Advanced onboard processing capabilities and robust driver support simplify system integration while maximizing throughput. Teledyne DALSA Frame Grabbers are engineered for seamless compatibility with cameras from a wide range of manufacturers, enabling flexible deployment across diverse imaging platforms. With scalable configurations optimized for Camera Link, Camera Link HS, GigE, CoaXPress, and other leading interfaces, they provide an ideal solution for high-speed, high-resolution imaging environments. Frame Grabbers are specialized capture boards focused on capturing individual, high-resolution, or non-standard frames for machine vision applications.