

WF 15X Eyepiece with 16mm FOV



#68-774 + #68-782 + #68-785



Stock **#68-778** 1 In Stock

-

1

+

₹13,590

ADD TO CART

Volume Pricing	
Qty 1-4	₹13,590 each
Qty 5+	₹12,870 each
Need More?	Request Quote

Product Downloads

General	
Wide Field	Type:
Physical & Mechanical Properties	
16.00	Field of View (mm):
	Diameter of Compatible Reticle (mm):

20.00	
Optical Properties	
16.00	Field Stop Diameter (mm):
15X	Magnification:
Regulatory Compliance	
View	Certificate of Conformance:
China	Country of Origin:
Edmund Optics India Private Limited	Imported By:

Product Details

- Capable of Achieving Magnifications from 2.4X - 320X
 - Modular Design for Maximum Customizability
 - Ergonomic Option to Prevent Repeat Use Injuries
 - Requires [#88-609](#) for 0.3X or 0.5X Objectives
- These Z Series Modular Zoom Stereo Microscopes are the perfect choice to build a new inspection system with easy to use components. With 3 zoom range options and multiple objectives and eyepieces, these systems can be customized to meet your exact needs. Optional components include a photoport insert and C-Mount adapter to connect directly to C-Mount cameras, as well as, [LED Ring Light Illuminators](#). When utilizing the 0.3X or 0.5X objectives, the Riser Adapter, [#88-609](#), is required.

Technical Information

Description				Stock No.
Main Body	One Required	0.8X - 8.0X Zoom Body Z Series Microscope, Z10		#68-772
		0.8X - 6.4X Zoom Body Z Series Microscope, Z8		#68-773
		0.8X - 5.0X Zoom Body Z Series Microscope, Z6		#68-774
Viewing Head	One Required	Binocular Microscope Head 20° Incline		#68-775
		Ergonomic Microscope Head 0-35° Incline		#68-776
Eyepieces	Two Required	WF 10X Eyepiece with 24mm FOV, Compatible w/ 26.5mm Reticle		#68-777
		WF 15X Eyepiece with 16mm FOV, Compatible w/ 20.0mm Reticle		#68-778
		WF 20X Eyepiece with 12.5mm FOV, Not Reticle Compatible		#68-779
Objective	One Required	0.3X Achromatic Z Series Objective, 0.03 NA, 280mm WD		#68-780
		0.5X Plan Apochromatic Z Series Objective, 0.05 NA, 126mm WD		#68-781
		1.0X Plan Apochromatic Z Series Objective, 0.09 NA, 78mm WD		#68-782
		2.0X Plan Apochromatic Z Series Objective, 0.02 NA, 32.5mm WD		#68-783
Riser Objective	One Required, if using 0.3X or 0.5X Objective	Rise Adapter		#88-609
Stand	One Required	Standard Microscope Stand with 76mm Holder		#68-784
		Variable LED Microscope Stand with 76mm Holder		#68-785

Objective							
Objective	Working Distance (mm)	10X Eyepieces					
		Z10 (0.8X - 8.0X)		Z8 (0.8X - 6.4X)		Z6 (0.8X - 5.0X)	
		Magnification	FOV (mm)	Magnification	FOV (mm)	Magnification	FOV (mm)
0.3X	280	2.4X - 24X	100 - 10	2.4X - 19.5X	100 - 12.3	2.4X - 15X	100 - 16
0.5X	126	4X - 40X	60 - 6	4X - 32.5X	60 - 70.4	4X - 25X	60 - 9.6
1.0X	78	8X - 80X	30 - 3	8X - 65X	30 - 3.7	8X - 50X	30 - 4.8
2.0X	32.5	16X - 160X	15 - 1.5	16X - 130X	15 - 1.85	16X - 100X	15 - 2.4
Objective	Working Distance (mm)	15X Eyepieces					
		Z10 (0.8X - 8.0X)		Z8 (0.8X - 6.4X)		Z6 (0.8X - 5.0X)	
		Magnification	FOV (mm)	Magnification	FOV (mm)	Magnification	FOV (mm)
0.3X	280	3.6X - 36X	66.7 - 6.67	3.6X - 29.3X	66.7 - 8.2	3.6X - 22.5X	66.7 - 10.67
0.5X	126	6X - 60X	40 - 4	6X - 52X	40 - 4.9	6X - 37.5X	40 - 6.4
1.0X	78	12X - 120X	20 - 2	12X - 97.5X	20 - 2.5	12X - 75X	20 - 3.2
2.0X	32.5	24X - 240X	10 - 1	24X - 195X	10 - 1.23	24X - 150X	10 - 1.6
Objective	Working Distance (mm)	20X Eyepieces					
		Z10 (0.8X - 8.0X)		Z8 (0.8X - 6.4X)		Z6 (0.8X - 5.0X)	
		Magnification	FOV (mm)	Magnification	FOV (mm)	Magnification	FOV (mm)
0.3X	280	4.8X - 48X	50 - 5	4.8X - 39X	50 - 6.15	4.8X - 30X	50 - 8

0.5X	126	8X- 80X	30 - 3	8X- 65X	30 - 3.7	8X- 50X	30 - 4.8
1.0X	78	16X- 160X	15 - 1.5	16X- 130X	15 - 1.85	16X- 100X	15 - 2.4
2.0X	32.5	32X- 320X	7.5 - 0.75	32X- 260X	7.5 - 0.9	32X- 200X	7.5 - 1.2
