

Triple Bandpass Green-Red-NIR Filter M37



Stock #74-604 NEW 1 In Stock

⊖ 1 ⊕ ₹35,496

ADD TO CART

Volume Pricing	
Qty 1+	₹35,496 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Type:
Triple Bandpass Mounted Imaging Filter

Model Number:
TB550/660/850-37

Full Width-Half Max FWHM Range (nm):
20nm, 20nm, 45nm ±10 nm

Physical & Mechanical Properties

39 **Outer Diameter (mm):**

2mm **Substrate Thickness (mm):**

Optical Properties

Green-Red-NIR **Color:**

40/20 **Surface Quality:**

≥85% **Transmission (%):**

543-558nm, 653-668nm, 835-865nm **Transmission Wavelength (nm):**

Threading & Mounting

M37 x 0.75 **Filter Thread:**

5.2 **Mount Thickness (mm):**

Regulatory Compliance

[View](#) **Certificate of Conformance:**

PRODUCT DETAILS

- Block and Transmit Desired Key VIS and NIR Spectral Bands with One Filter
- Remove The Need for Dual Sensor Setups
- Anti-Reflection Coating for Durability and Performance
- Various Mounting Thread Options Available

Multi-Band Machine Vision Bandpass Filters feature both double or triple bandpass options in one filter, allowing for greater flexibility in system design. These filters are designed with up to ≥90% transmission in the visible (VIS) or near-infrared (NIR) spectra with various wavelength range combinations available. Additionally, these filters are AR coated for optimal transmission and feature a hard-coated, single-substrate design with superior surface quality to maximize optical performance. Multi-Band Machine Vision Bandpass Filters ensure accurate color reproduction by blocking unwanted wavelengths, eliminating the need for dual-sensor imaging. These filters are ideal for surveillance applications such as, security and intelligent traffic management, as well as normalized difference vegetation index (NDVI) imaging applications.

Note: Other filter threads are available upon request.