

# Ultra-Thin Polarizer, 1310nm, 10 x 10mm, Uncoated



Ultra-Thin Polarizer, Square

Stock **#26-641** 1 In Stock

-

1

+

₹32,308

ADD TO CART

| Volume Pricing |                               |
|----------------|-------------------------------|
| Qty 1+         | ₹32,308 each                  |
| Need More?     | <a href="#">Request Quote</a> |

Product Downloads

| Physical & Mechanical Properties |                   |
|----------------------------------|-------------------|
| 10 x 10 +0/-0.1                  | Dimensions (mm):  |
| 0.09 ± 0.025                     | Thickness (mm):   |
| Optical Properties               |                   |
| Uncoated                         | Coating:          |
| >10,000:1                        | Extinction Ratio: |

|                                                       |                                          |
|-------------------------------------------------------|------------------------------------------|
| Sodium Silicate Glass Doped with Silver Nanoparticles | Substrate: <div></div>                   |
| 40-20                                                 | Surface Quality:                         |
| >87                                                   | Transmission (%):                        |
| 1260 - 1360                                           | Wavelength Range (nm):                   |
| 10 W/cm <sup>2</sup>                                  | Damage Threshold, By Design: <div></div> |
| ± 20°                                                 | Acceptance Angle (°):                    |
| <3 λ                                                  | Transmitted Wavefront Error, RMS:        |

Environmental & Durability Factors

|             |                             |
|-------------|-----------------------------|
| -50 to +400 | Operating Temperature (°C): |
|-------------|-----------------------------|

Regulatory Compliance

|                                     |                             |
|-------------------------------------|-----------------------------|
| Compliant                           | RoHS 2015:                  |
| View                                | Certificate of Conformance: |
| Compliant                           | REACH 241:                  |
| Germany                             | Country of Origin:          |
| Edmund Optics India Private Limited | Imported By:                |

## Product Details

- NEW LOWER PRICE!
- Lightweight 90µm Thick Substrate
- >10,000:1 Extinction Ratio
- Excellent Resistance to Temperature, Chemicals, and Harsh Environments
- Range of Standard Sizes, Coatings, and Custom Options Available

Ultra-Thin Nanoparticle Polarizers are a lightweight 90µm thick alternative to traditional polarizers while providing a high transmission and an extinction ratio of >10,000:1. Constructed from sodium silicate glass substrate doped with prolate silver nanoparticles, these polarizers provide high temperature stability up to +400°C, chemical resistance, and resistance to UV radiation and bleaching. These polarizers are available uncoated, Single-Side AR coated, or Double-Side AR coated and cover wavelength ranges from 366-1600nm. Ultra-Thin Nanoparticle Polarizers design are ideal for use in telecom, medical, and aerospace applications as well as in optical isolators, polarization interferometry, and improving signal-to-noise ratio.

## Custom

Edmund Optics offers comprehensive custom manufacturing services for optical and imaging components tailored to your specific application requirements. Whether in the prototyping phase or preparing for full-scale production, we provide flexible solutions to meet your needs. Our experienced engineers are here to assist—from concept to completion.

Our capabilities include:

- Custom dimensions, materials, coatings, and more
- High-precision surface quality and flatness
- Tight tolerances and complex geometries
- Scalable production—from prototype to volume

Learn more about our [custom manufacturing capabilities](#) or submit an inquiry [here](#).