

[See all 13 Products in Family](#)

Zaber 20mm, X-LDA-AEZ Vertical Translation Stage

See More by [Zaber™](#)



Stock #75-564 NEW **1 In Stock**

MRP ₹9,01,957

📌 Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹9,01,957 each
Need More?	Request Quote

Product Downloads

General

Metric Type:

Yes Encoder:

Yes Manual Control/ LED Indicators:

Zaber Technologies Inc. Manufacturer:

Note:

Requires a 24-48 VDC power supply and either [#15-295](#) for USB connectivity or [#15-297](#) for RS-232 connectivity. A data cable ([#15-296](#) or [#15-299](#)) can be used to daisy chain multiple stages together to control simultaneously.

Type of Motor:
Moving Magnet Track Linear Mtor

Encoder Type:
Linear Analog Encoder

Physical & Mechanical Properties

Type of Movement:
Linear (X)

Guide System:
Crossed-Roller Bearing

Stage Size (mm):
191 x 110

Travel (mm):
20

Accuracy (µm):
1.5

Height (mm):
37.4

Load Capacity (kg):
1.63

Repeatability (µm):
<0.2

Speed (mm/s):
0.0000061 - 700

Weight (kg):
1.29

Electrical

Maximum Operating Current (mA):
3000

Hardware & Interface Connectivity

Type of Drive:
Moving Magnet Track Linear Mtor

Power Supply:
Power Supply Required and Sold Separately.
USA: [#70-960](#)
Europe: [#70-960](#)
Japan: [#23-662](#)
Korea: [#33-773](#) + [#15-304](#)
China: [#70-960](#)

Computer Interface:
RS-232

Environmental & Durability Factors

Operating Temperature (°C):
0 - 50

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 247:
[Compliant](#)

Country of Origin:
Canada

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- 25, 75, 150mm Travel Options
- Up to 800mm/s Speed
- High Repeatability and Accuracy

Zaber™ High Precision Linear Motorized Stages are computer-controlled linear stages that utilize a moving magnet track linear motor and centrally located encoder to accurately and precisely position optical components or subsystems. These stages can connect directly to a computer's USB or RS-232 port and are compatible with [Zaber Launcher](#) and [Zaber's Motion Library](#) for quick set up and intuitive automation and control. The linear analog encoder has 1nm count size ensuring 1.5µm positional accuracy, 200µm repeatability, and consistent minimal incremental movement steps down to 20nm. Zaber™ High Precision Linear Motorized Stages are driven by non-cogging ironless linear motors which allow for speeds up to 800 mm/s with a minimum speed and speed resolution of 0.61mm/s. These stages are designed with metric tapped holes for mounting and an indexed knob and push switch for manual control when needed.

Note: A 48 VDC universal power supply, data cables for daisy chaining, and computer interface cables (USB or RS-232) are sold separately as accessories.
