

[See all 3 Products in Family](#)

UV Radiometer Unit



UV Radiometer Unit, #88-136

Stock **#88-136** **1 In Stock**

MRP ₹1,23,192

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹1,23,192 each
Need More?	Request Quote

Note: This item requires accessories for use | [Learn More](#)

Product Downloads

General

3.5 digit LCD **Type of Display:**

2.8 readings/sec **Conversion Rate:**

Physical & Mechanical Properties

0.3 **Weight (kg):**

157 x 51 x 91

Dimensions (mm):

± 2

Accuracy (%):

Electrical

Intensity Range:

Switchable:
0 – 20 mW/cm²
0 – 200 μW/cm²
0 – 2000 μW/cm²

Hardware & Interface Connectivity

Power Requirement:

9 V Battery (not included)

Regulatory Compliance

Certificate of Conformance:

[View](#)

Country of Origin:

United States

Imported By:

Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

- Designed to Detect UV Wavelengths from 250 – 380nm
- NIST Certified Sensors
- 9V Battery Provides up to 120 Hours of Operation
- Requires One NIST Traceable Sensor for Operation

The NIST Certified UV Radiometer is ideal for inspecting ultraviolet light sources in a variety of quality control applications. The NIST Certified UV Radiometer is powered by a standard 9V battery for up to 120 hours of operation. Three NIST certified interchangeable sensors are available to detect a wide range of ultraviolet wavelengths from 250 – 380nm. The NIST Certified UV Radiometer's range switch allows the selection of three intensity ranges.

Note: The UV Radiometer Unit ([#88-136](#)) requires one NIST Traceable Sensor ([#88-137](#), [#88-138](#), or [#88-139](#)) for operation.