

TECHSPEC® UV-VIS ND Filter Kit, 12.5mm Diameter Filters



Stock #48-626 1 In Stock

-

1

+

₹55,118

Price inclusive of all taxes

ADD TO CART

Volume Pricing	
Qty 1+	₹55,118 each
Need More?	Request Quote

Product Downloads

General	
Filters Included :	0.3, 0.5, 1.0, 1.3, 1.5, 2.0, 2.5, 3.0
Type:	Neutral Density Filter
Physical & Mechanical Properties	
Diameter (mm):	12.50
Optical Properties	

Fused Silica (Corning 7980)		Substrate: ☐
Metallic Based ND		Coating:
250 - 700	Blocking Wavelength Range (nm):	
0.25 - 0.7	Wavelength Range (μm):	

Regulatory Compliance	
View	Certificate of Conformance:
United States	Country of Origin:
Edmund Optics India Private Limited 267, Greystone Building, Second Floor, 6th Cross Rd, Binnamangala, Stage 1, Indiranagar, Bengaluru, Karnataka, India 560038 Phone: +91- 80-6845 0000	Imported By:

Product Details

- Ideal for 250-700nm Sources
 - Optical Densities Ranging from 0.3 to 3.0
- TECHSPEC® UV-VIS Neutral Density (ND) Filters are spectrally flat from 250 to 700nm and feature outstanding parallelism and surface characteristics. This combination of high tolerance and broadband performance makes these filters ideal for attenuating a wide range of sources. The filters are suitable for low power laser applications and can be stacked to obtain a variety of optical densities. TECHSPEC UV-VIS Neutral Density (ND) should have their mirrored side oriented toward the source at a 0° angle of incidence. Optical Densities of 0.5, 1.0, 1.5, 2.0, 2.5 and 3.0 available in a [Pre-Loaded Filter Wheel](#).
- Note:** Due to supply chain issues, our kits may be delivered with an alternative packaging solution in place of a wooden box. For any questions, please contact kits@edmundoptics.com.

TECHSPEC® UV-VIS Reflective Neutral Density Filter Kit

Each kit includes 8 filters in optical density values of 0.3, 0.5, 1.0, 1.3, 1.5, 2.0, 2.5, and 3.0. The kit is ideal for determining precise system optical density requirements. Custom densities are available for OEM applications.