

[See all 12 Products in Family](#)

## VIS-NIR Fiber Patch Cord, 200 μm Core, Stainless steel BX

See More by [Ocean Optics](#)



Stock #90-547 NEW **1 In Stock**

⊖ 1 ⊕ MRP ₹28,886

● Price inclusive of all taxes

**ADD TO CART**

### Volume Pricing

Qty 1+	₹28,886 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

QP200-2-VIS-BX **Model Number:**

### Physical & Mechanical Properties

2 **Length (m):**

200 **Core Diameter (μm):**

Stainless-steel BX **Jacket Material:**

## Optical Properties

0.22 **Numerical Aperture NA:**

400 - 2100 **Wavelength Range (nm):**

## Hardware & Interface Connectivity

SMA **Connector:**

## Material Properties

Polyimide **Buffer Material:**

## Regulatory Compliance

[Compliant](#) **RoHS 2015:**

[View](#) **Certificate of Conformance:**

[Compliant](#) **Reach 250:**

China **Country of Origin:**

**Imported By:**  
Edmund Optics India Private Limited  
267, Greystone Building, Second Floor,  
6th Cross Rd, Binnamangala,  
Stage 1, Indiranagar, Bengaluru,  
Karnataka, India 560038  
Phone: +91- 80-6845 0000

## Product Details

- Connects Directly with Ocean Optics Spectrometers & Accessories
- Broad Wavelength Coverage: VIS-NIR, SR, and XSR Fibers Optimized for 180–2100 nm
- Solarization-Resistant Fibers Maintain Signal Accuracy Under Harsh UV
- Multiple Jacketing Choices for Durability and Tight Bend Radius Needs

Ocean Optics offers a complete line of premium optical fiber patch cords compatible with [Ocean Optics spectrometers](#) to suit a range of VIS-NIR and UV-NIR spectroscopy needs. Use them as illumination or read fibers to connect spectrometers, light sources, probes, or sampling accessories with maximum transmission efficiency and minimal signal loss. Choose standard visible-NIR assemblies for broadband applications or select solarization-resistant options to maintain signal fidelity when working with high UV power. Ocean Optics Spectrometer Patch Cords are available with a range of jacketing options designed to enhance durability and accommodate applications requiring a tight bend radius.

**VIS-NIR Patch Cords (400–2100 nm):** Best for routine broadband spectroscopy with minimal OH content, minimizing light absorption caused by hydroxyl ions (OH<sup>-</sup>), for efficient NIR transmission.

**Solarization-Resistant Patch Cords (200–1100 nm):** Ideal for UV-NIR work where standard silica fibers degrade under high UV exposure.

**Extreme Solarization-Resistant Patch Cords (180–800 nm):** Essential for deep-UV applications where the highest UV resistance is required.