

[See all 2 Products in Family](#)

White LED Spot Light



Stock #63-339 CLEARANCE **5 In Stock**

MRP ₹44,599

Price inclusive of all taxes

ADD TO CART

Volume Pricing

Qty 1+	₹44,599 each
Need More?	Request Quote

Product Downloads

General

100,000 **LED Lifetime (hours):**

LED Illuminator **Type of Illumination:**

Spot Light **Geometry:**

Strobed or Constant **Illumination Mode:**

Physical & Mechanical Properties

35.00 Diameter (mm):

29.5 Height (mm):

Optical Properties

White Color:

10.00 Spot Size at 50mm Working Distance (mm):

N/A Irradiance at 50mm (W/m²):

Electrical

400mA Maximum Input Current:

Hardware & Interface Connectivity

Power Supply Required and Sold Separately.
USA: [#59-433](#)
Europe: Not Available
Japan: [#59-433](#)
Korea: Not Available
China: [#59-433](#)

Threading & Mounting

M3 Mounting Threads:

Regulatory Compliance

Compliant RoHS 2015:

Compliant Reach 209:

View Certificate of Conformance:

Ireland Country of Origin:

Imported By:
Edmund Optics India Private Limited
267, Greystone Building, Second Floor,
6th Cross Rd, Binnamangala,
Stage 1, Indiranagar, Bengaluru,
Karnataka, India 560038
Phone: +91- 80-6845 0000

Product Details

[#59-433](#) Universal Power Supply and [#59-371](#) DC Current Controller are required for operating all spot lights. [#63-342](#) Area and Spot Light Heat Sink is recommended to maintain performance and optimize product lifetime.

- Variable Intensity with DC Current Controller
- Excellent Uniformity
- 60,000 Hour Product Lifetime
- [Heat Sinks and Power Supplies](#) Sold Separately

Compact LED Spot Lights provide the high-power illumination required in machine vision, biomedical, fluorescence, and strobing applications. Each LED module contains four M3 mounting holes on a 29mm diameter circle. The universal power supply, which accepts a 90 - 245VAC input, ships with clip-on adapters for the US, Europe, and UK. Through the DIN rail mountable DC current controller, LED intensity can be adjusted manually via a potentiometer or by supplying a 0 - 5V analog control input. The DC current controller is designed to deliver up to 400mA at 24V.

Note: [#59-433](#) Universal Power Supply and [#59-371](#) DC Current Controller are required for operating all spot lights. [#63-342](#) Area and Spot Light Heat Sink is recommended to maintain performance and optimize product lifetime.