




NOTES:

- SUBSTRATE:
BOROFLOAT®
- COATING PERFORMANCE (APPLY ACROSS COATING APERTURE)
T(AVG) <1.0% @ 390 - 570nm
T(AVG) >85% @ 620 - 750nm
T(ABS) <2.0% @ 415 - 550nm
T(ABS) >80% @ 630 - 750nm


3. FINE GROUND SURFACE

- ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	 Edmund Optics®			
SHAPE	PLANO	PLANO		TITLE	25mm Diameter, Red Dichroic Filter	
SURFACE QUALITY	80-50	80-50		DWG NO	52528	SHEET 1 OF 1
CLEAR APERTURE	≥85%	≥85%				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				
			ALL DIMS IN	mm		