

## NOTES:

- SUBSTRATE MATERIAL:
   OPTICAL GRADE GERMANIUM
- 2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 WITHIN 1 ARCMIN
- 3. COATING(APPLY ACROSS CLEAR APERTURE) \$1 & \$2: R(AVG) < 3% FROM 3.0 TO 5.0 µm
- 4. FINE GROUND SURFACE
- 5. PROTECTIVE BEVEL AS NEEDED





## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

						Edmund Option	C®
	\$1	\$2					
SHAPE	PLANO	PLANO				40mm Dig v 4 0mm Thick 2 5um AB Co	atina
SURFACE ACCURACY AT 10.6µm (P-V)	1/10 WAVE	1/10 WAVE				40mm Dia. x 4.0mm Thick 3-5µm AR Coating, Ge Window	
SURFACE QUALITY	60 - 40	60 - 40				L CUE	
MIN CLEAR APERTURE	Ø36.0	Ø36.0	ALL DIMS IN	mm	DWG NO	89567	SHEET 1 OF 1