



NOTES:

1. ALLOWABLE OPTICAL MATERIAL: GRADE A FINE ANNEALED  
SCHOTT: N-BK7
2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN 5 ARCMIN
3. COATING (APPLY ACROSS COATING APERTURE)  
S1: NONE  
S2: NONE

4. SIX SIDEWALLS:  
SURFACE ACCURACY: COMMERCIAL POLISH



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE PARTS TO THIS DRAWING**

**EO**® Edmund Optics®

|                             | S1      | S2      |                     |    |
|-----------------------------|---------|---------|---------------------|----|
| SHAPE                       | PLANO   | PLANO   | EFL<br>(AT 587.6nm) | NA |
| SURFACE ACCURACY AT 632.8nm | 1 WAVE  | 1 WAVE  | BFL<br>(AT 587.6nm) | NA |
| SURFACE QUALITY             | 60 - 40 | 60 - 40 | ALL DIMS IN         | mm |

|        |                              |
|--------|------------------------------|
| TITLE  | 6mm HEX LIGHT PIPE, 150mm lg |
| DWG NO | 63087                        |