


NOTES:

1. ALLOWABLE OPTICAL MATERIAL: GRADE A FINE ANNEALED
SCHOTT: N-BK7
2. SURFACE S2 TO BE PARALLEL WITH SURFACE S1 TO WITHIN 5 ARCMIN
3. COATING (APPLY ACROSS COATING APERTURE)
S1: NONE
S2: NONE

4. FOUR SIDEWALLS:
SURFACE ACCURACY: COMMERCIAL POLISH



FOR INFORMATION ONLY:
DO NOT MANUFACTURE PARTS TO THIS DRAWING

| | S1 | S2 | | |
|-----------------------------|---------|---------|---------------------|----|
| SHAPE | PLANO | PLANO | EFL (AT 587.6nm) | NA |
| SURFACE ACCURACY AT 632.8nm | 1 WAVE | 1 WAVE | BFL (AT 587.6nm) | NA |
| SURFACE QUALITY | 60 - 40 | 60 - 40 | ALL DIMS IN | mm |

EO[®] Edmund Optics[®]

TITLE 2.5mm SQUARE TAPERED LIGHT PIPE, 50mm, 2X
DWG NO 63103