





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



LONGPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. 001	S1	S2
SHAPE	PLANO	PLANO
SPECTRAL TRANSMITTANCE $t_{IP}(\%)$	97	97
PASSBAND LIMIT $1 \lambda_{p1}$ (nm)	900	900
CUT-OFF POSITION λ_c (nm)	780±9	780±9
STOPBAND LIMIT λ_s (nm)	610	610
WAVELENGTH	IR	IR
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

 **Edmund Optics®**



ALL DIMS IN

mm

TITLE

Ø25.4mm, SCHOTT RG-780 LONGPASS FILTER

DWG NO

32757

SHEET
1 OF 1