





FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING



LONGPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. 001	S1	S2
SHAPE	PLANO	PLANO
SPECTRAL TRANSMITTANCE $t_{IP}(\%)$	97	97
PASSBAND LIMIT 1 λ_{p1} (nm)	120	120
CUT-OFF POSITION λ_c (nm)	850±9	850±9
STOPBAND LIMIT λ_s (nm)	700	700
WAVELENGTH	IR	IR
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

 **Edmund Optics®**



ALL DIMS IN

mm

TITLE

Ø25.4mm, SCHOTT RG-850 LONGPASS FILTER

DWG NO

32759

SHEET
1 OF 1