





**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**



LONGPASS FILTER

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	VALUE
SHAPE	PLANO
SPECTRAL TRANSMITTANCE $\tau_{ip}(\%)$	97
PASSBAND LIMIT λ_p (nm)	1200
CUT-OFF POSITION λ_c (nm)	850±9
STOPBAND LIMIT λ_s (nm)	700
WAVELENGTH	IR
BEVEL	PROTECTIVE AS NEEDED

 **Edmund Optics®**



ALL DIMS IN

mm

TITLE

Ø50mm, SCHOTT RG-850 LONGPASS FILTER

DWG NO

66107

SHEET
1 OF 1