



NOTES:

- 1. SUBSTRATE:
FLOAT GLASS
- 2. ANTI REFLECTION SURFACE TREATMENT (APPLY ACROSS CLEAR APERTURE)
AOI: 0°
S1 & S2: Ravg ≤0.5% @ 425 - 700nm


3. GROUND EDGES

4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

		S1	S2	 Edmund Optics®		
SHAPE		PLANO	PLANO		TITLE	Ø254mm x 3mm HIGH EFFICIENCY WINDOW
SURFACE QUALITY		80-50	80-50			
CLEAR APERTURE		≥90%	≥90%	ALL DIMS IN	DWG NO	48860
BEVEL		PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	mm		SHEET 1 OF 1