NOTES:

1. SUBSTRATE: FLOAT GLASS


2. ANTI REFLECTION SURFACE TREATMENT (APPLY ACROSS CLEAR APERTURE)


AOI: 0°


S1 & S2: Ravg ≤0.5% @ 425 - 700nm



4. ROHS COMPLIANT







FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2		
SHAPE	PLANO	PLANO		
SURFACE QUALITY	80-50	80-50		
CLEAR APERTURE	≥90%	≥90%		
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED		

			Edmund Optics®	
THIRD ANGLE _ PROJECTION		TITLE	Ø25.4mm x 1mm HIGH EFFICIENCY WIN	1DOM
ALL DIMS IN	mm	DWG NO	48924	SHEET 1 OF 1