
NOTES:


- 1. SUBSTRATE: FLOAT GLASS
- 2. WAVELENGTH RANGE: 350 2000nm


FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING





- POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS APPLY ACROSS CLEAR APERTURE
- 5. ROHS COMPLIANT





SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

Edmund Optics

	S 1	S2	THIRD ANGLE PROJECTION		TITLE	25mm DIAMETER FLOAT GLASS WINDOW	
SHAPE	PLANO	PLANO					
SURFACE FLATNESS	4 - 6λ	4 - 6λ		 			CHEET
COATING APERTURE	UNCOATED	UNCOATED	ALL DIMS IN	mm	DWG NO	30773	SHEET 1 OF 1