

NOTES:

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

1. SUBSTRATE: FUSED SILICA
2. PARALLELISM : 30 ARCSEC
3. COATING SPECIFICATION:




ENHANCED ALUMINUM

S1: R(avg) >95% @ 450 - 650nm

S2: NONE

4. POWER, IRREGULARITY, AND SURFACE QUALITY SPECIFICATIONS  
APPLY ACROSS CLEAR APERTURE


5. ROHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**EO**® **Edmund Optics**®

|                  | S1                   | S2                   |
|------------------|----------------------|----------------------|
| SHAPE            | PLANO                | PLANO                |
| SURFACE QUALITY  | 20-10                | COMMERCIAL POLISH    |
| SURFACE FLATNESS | $\lambda/20$         | N/A                  |
| BEVEL            | PROTECTIVE AS NEEDED | PROTECTIVE AS NEEDED |

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

|        |  |       |        |
|--------|--|-------|--------|
| TITLE  | 30.0 x 30.0mm, $\lambda/20$ , ENHANCED ALUMINUM MIRROR |       |        |
| DWG NO | 34363  | SHEET | 1 OF 1 |