



NOTES:


1. SUBSTRATE: Float Glass
2. COATING (APPLY ACROSS CLEAR APERTURE)
S1: Enhanced Aluminum (450-650nm)
R(AVG) ≥95% @ 450 - 650nm @ 45°

S2: NONE
3. EDGES SEAMED
4. RoHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	S1	S2	 Edmund Optics®				
SHAPE	PLANO	PLANO			TITLE	75 x 75mm Enhanced Aluminum, 4-6λ Mirror	
SURFACE QUALITY	60-40	N/A			DWG NO	48452	SHEET 1 OF 1
SURFACE FLATNESS	4 - 6λ	N/A					
CLEAR APERTURE	71.25 x 71.25	N/A	ALL DIMS IN	mm			
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED					