

NOTES:




1. SUBSTRATE MATERIAL: Fused Silica
2. SURFACE S2 TO BE PARALLEL WITH S1 TO 30 arcsec
3. COATING (APPLY ACROSS CLEAR APERTURE)

S1: Enhanced Aluminum  
R(avg) >95% @ 450 - 650nm

S2: NONE

 FINE GRIND SURFACE


5. RoHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

 **Edmund Optics®**

REV. A	S1	S2	THIRD ANGLE PROJECTION 		TITLE	20mm Square, Enhanced Aluminum Coated, λ/10 Mirror	
SURFACE QUALITY	20-10	COMMERCIAL POLISH	ALL DIMS IN	mm	DWG NO	64014	SHEET 1 OF 1
SURFACE FLATNESS	λ/10	NA			TITLE	20mm Square, Enhanced Aluminum Coated, λ/10 Mirror	
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED					