
## NOTES:

- 1. SUBSTRATE: N-BK7
- 2. S2 TO BE PARALLEL WITH S1 TO <30 arcsec
- 3. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: NONE



5. Rohs Compliant



## FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2
SHAPE	PLANO	PLANO
SURFACE QUALITY	40-20	40-20
WAVELENGTH RANGE	350 - 2200nm	350 - 2200nm
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

			<b>Edmund Optics</b>		
	THIRD ANGLE _ PROJECTION	$\phi \lhd$	TITLE	30mm DIAMETER UNCOATED, ULTRA-TH BK7 WINDOW	HIN N-
)	ALL DIMS IN	mm	DWG NO	66189	SHEET 1 OF 1