NOTES:


1. WAVELENGTH RANGE:: 400 - 700nm


2. COATING: UNCOATED


FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

FINE GRIND SURFACE

4. ROHS COMPLIANT







SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2
SHAPE	PLANO	PLANO
SURFACE QUALITY	80-50	80-50
SURFACE ACCURACY	COMMERCIAL POLISH	H COMMERCIAL POLISH
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

	THIRD ANGLE - PROJECTION	$\phi \Box$	TITLE
)	ALL DIMS IN	mm	DWG NO

Edmund Optics ®				
TITLE	50 x 50mm WHITE DIFFUSING GLAS	S		
DWG NO	34476	SHEET 1 OF 1		