



NOTES:

- 1. SUBSTRATE:
BOROFLOAT®
- 2. COATING SPECIFICATION:
S1: Enhanced Aluminum (250-700nm)
R(AVG) >89% @ 250 - 450nm
R(AVG) >85% @ 250 - 700nm



3. FINE GROUND SURFACE

- 4. ROHS COMPLIANT



**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

			 Edmund Optics®			
SHAPE	S1 PLANO	S2 PLANO		TITLE	40 x 40mm UV Enhanced Aluminum, λ/4 Mirror	
SURFACE QUALITY	60-40	COMMERCIAL POLISH		DWG NO	63173	SHEET 1 OF 1
CLEAR APERTURE	34.00 x 34.00	N/A				
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED				
			ALL DIMS IN	mm		