
NOTES:


- 1. SUBSTRATE MATERIAL: FLOAT GLASS
- 2. ROHS COMPLIANT
- 3. COATING (APPLY ACROSS CLEAR APERTURE)

S1: 30% R ±5% @ 550nm 70% T ±5% @ 550nm

S2: AR ¼λ MgF2 @ 550nm







PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

REV. A	\$1	\$2			
SHAPE	PLANO	PLANO			
SURFACE QUALITY	80-50	80-50			
SURFACE FLATNESS	4 - 6λ	4 - 6λ			
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED			

			B	Edmund Optic	S®
	THIRD ANGLE PROJECTION		TITLE 25	4 x 356mm, 30 R/70 T, PLATE BEAMSPLITTER)
<u> </u>	ALL DIMS IN	mm	DWG NO	43363	SHEET

TITLE 25	54 x 356mm, 30 R/70 T, PLATE BEAMSPLITTER