



**NOTES:**

1. SUBSTRATE: CaF2 / FUSED SILICA / CaF2
2. COATING: UNCOATED
3. WAVELENGTH RANGE: 193 - 1000nm



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

EFL @ 248nm	135	 <b>Edmund Optics®</b>	135 mm EFL UNCOATED, UV-TO-NIR CORRECTED TRIPLET	
BFL @ 248nm	129.31			
THIRD ANGLE PROJECTION 	TITLE			
ALL DIMS IN	mm	DWG NO	47312	SHEET 1 OF 1