





NOTES:

1. COATING (APPLY ACROSS CLEAR APERTURE)

S1: R(avg) >96% @ 700 - 2000
 R(avg) >96% @ 2000 - 10000nm

S2: NONE


**FOR INFORMATION ONLY:
 DO NOT MANUFACTURE
 PARTS TO THIS DRAWING**



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
 DIMENSIONS ARE FOR REFERENCE ONLY



REV. A	S1	S2
SURFACE QUALITY	60-40	60-40
SURFACE FLATNESS	4 - 6λ	4 - 6λ

THIRD ANGLE PROJECTION 

ALL DIMS IN mm

TITLE	PROTECTED GOLD C-MOUNTED FIRST SURFACE MIRROR	
DWG NO	36153	SHEET 1 OF 1