



NOTES:



- 1. COATING:  
S1: SPECTRAL BLACK™  
THICKNESS (µm) 3-7
- 2. ABSORBANCE: 99.9% (0-10°)%
- 3. ABRASION RESISTANCE: MODERATE
- 4. HUMIDITY RESISTANCE: MIL-C-48497A
- 5. OPERATING TEMPERATURE (°C): -196 to 350
- 6. WAVELENGTH RANGE: 0.3 - 14



DETAIL A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

 Edmund Optics®			
THIRD ANGLE PROJECTION 		TITLE	Spectral Black No Adhesive Foil Sheet 200 x 300mm
ALL DIMS IN	mm	DWG NO	12685
			SHEET 1 OF 1