




NOTES:

1. COATING:  
S1: MaxiBlack™  
THICKNESS (μm) 4 - 6
2. ABSORBANCE: 98%
3. ABRASION RESISTANCE: Moderate
4. HUMIDITY RESISTANCE: MIL-C-48497A
5. OPERATING TEMPERATURE: -50 to 150
6. WAVELENGTH RANGE: 0.3 - 5




DETAIL A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

**EO**® Edmund Optics®

THIRD ANGLE PROJECTION 		TITLE	MaxiBlack Low Outgassing Adhesive Polymer Film 200 x 600mm	
ALL DIMS IN	mm	DWG NO	13489	SHEET 1 OF 1