




NOTES:

1. COATING:
S1: MaxiBlack™
THICKNESS (μm) 4 - 6
2. ABSORBANCE: 98%
3. ABRASION RESISTANCE: Moderate
4. HUMIDITY RESISTANCE: MIL-C-48497A
5. OPERATING TEMPERATURE: -250 to 290
6. WAVELENGTH RANGE: 0.3 - 5



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO® Edmund Optics®

THIRD ANGLE PROJECTION		TITLE	MaxiBlack No Adhesive Polymer Film 200 x 600mm	
		DWG NO	13493	SHEET 1 OF 1