NOTES:


1. MATERIAL:


HOUSING: STAINLESS STEEL LENS: D-ZLaF52LA


2. COATING (APPLY ACROSS CLEAR APERTURE) R(AVG) <0.4% @ 600 - 1050nm

3. CLEAR APERTURE: 5.00 mm

4. RoHS: COMPLIANT







SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

Edmund Optics®

THIRD ANGLE TITLE 780nm Alignment, 0.40 NA Fiber Collimator w/ SMA Connector

ALL DIMS IN mm DWG NO 64772 SHEET 1 OF 1

