




NOTES:

1. MATERIAL:
HOUSING: STAINLESS STEEL
LENS: ECO 550
2. COATING (APPLY ACROSS CLEAR APERTURE)
R(AVG) <0.4% @ 350 - 600nm
3. CLEAR APERTURE: 8mm
4. RoHS: COMPLIANT




SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO® Edmund Optics®

| | | | | |
|--------------------------------------------------------------------------------------------------------------|----|--------|---------------------------------------------------------------|-----------------|
| THIRD ANGLE PROJECTION  | | TITLE | 543nm Alignment, 0.50 NA Fiber Collimator w/ SMA Connector | |
| ALL DIMS IN | mm | DWG NO | 64778 | SHEET 1 OF 1 |