


NOTES:

- 1. SUBSTRATE: POLYMER FILM XP40HT-40
- 2. WAVELENGTH RANGE: 400 - 700 nm
- 3. POLARIZATION EFFICIENCY (%): > 99.99
- 4. TRANSMISSION (%):
SINGLE: 40 ±2
PARALLEL: 32.2
CROSSED: <0.006
- 5. EXTINCTION RATIO: 5000:1
- 6. ROHS COMPLIANT



SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

EO[®] Edmund Optics[®]			
THIRD ANGLE PROJECTION		TITLE	600 x 500mm HIGH-TEMPERTURE LINEAR POLARIZING FILM (XP40HT-40)
ALL DIMS IN	mm	DWG NO	14349
			SHEET 1 OF 1