
NOTES:


- 1. SUBSTRATE: **FUSED SILICA**
- 2. S2 TO BE PARALLEL WITH S1 TO WITHIN < 1 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: R(AB\$) ≤ 0.25% AT 880nm R(AVG) ≤ 1.25% FROM 400-870nm R(AVG) ≤ 1.25% FROM 890-1000nm


FINE GRIND SURFACE

5. Rohs Compliant









PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	S2
SHAPE	PLANO	PLANO
SURFACE QUALITY	40-20	40-20
CLEAR APERTURE (mm)	Ø67.50	Ø67.50
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

			Edmund Optics ®	
THIRD ANGLE PROJECTION		TITLE	75mm DIA., 4mm THICK, VIS-NIR COATED, λ/4 FUSED SILICA WINDOW	
ALL DIMS IN	mm	DWG NO	14993	SHEET 1 OF

75mm DIA., 4mm THICK, VIS-NIR COATED,
$\lambda/4$ FUSED SILICA WINDOW

SHEET 1 OF 1