

TECHSPEC® IR-CUT BLUE SERIES

M12 IMAGING LENSES

#35-468 • 2mm • f/8.0

TECHSPEC® Blue Series M12 Imaging Lenses feature high resolution performance, along with the same great versatility of our TECHSPEC® Green Series M12 Imaging Lenses. Each lens consists of several precision glass elements mounted in a compact, aluminum housing. TECHSPEC® Blue Series M12 Imaging Lenses are ideal for automotive, industrial, and medical imaging application.



Focal Length:	2mm
Working Distance¹:	100mm - ∞
Max. Sensor Format:	1/3"
Camera Mount:	M12
Aperture (f/#):	f/8.0
Distortion %²:	<81.25%
Object Space NA³:	0.001223

1. From front housing 2. At 750mm W.D. 3. At Minimum W.D.

Magnification Range:	0X - 0.020X
Type:	M12 Lens
Length:	21.7mm
Weight:	9g
RoHS:	Compliant
Number of Elements (Groups):	6 (5)
AR Coating:	400-700nm MgF ₂

At Minimum W.D. (100mm)							
Sensor Size	1/4"	1/3"	1/2.5"	1/2"	1/1.8"	2/3"	1"
Field Of View ⁴	248.7mm - 100.4°	476.2mm - 133.2°	N/A	N/A	N/A	N/A	N/A

4. Horizontal FOV on Standard (4:3) sensor format. Min W.D.




Figure 1: Distortion at the maximum sensor format. Positive values correspond to pincushion distortion, negative values correspond to barrel distortion.




Figure 2: Relative illumination (center to corner)

In both plots, field points corresponding to the image circle of common sensor formats are included. Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

MTF & DOF: f/8.0
WD: 100mm
HORIZONTAL FOV: 478mm




Figure 3: Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for $\lambda = 486\text{nm}$ to 656nm . Included are the Tangential and Sagittal values for field points on center, at 70% of full field and the maximum sensor format. Solid black line indicates diffraction limit determined by f/#-defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




Figure 4: Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

MTF & DOF: f/8.0
WD: 250mm
HORIZONTAL FOV: 1173mm




Figure 5: Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for $\lambda = 486\text{nm}$ to 656nm . Included are the Tangential and Sagittal values for field points on center, at 70% of full field and the maximum sensor format. Solid black line indicates diffraction limit determined by $f/\#$ -defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




Figure 6: Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.

MTF & DOF: f/8.0
WD: 500mm
HORIZONTAL FOV: 2331mm




Figure 7: Image space polychromatic diffraction FFT Modulation Transfer Function (MTF) for $\lambda = 486\text{nm}$ to 656nm . Included are the Tangential and Sagittal values for field points on center, at 70% of full field and the maximum sensor format. Solid black line indicates diffraction limit determined by f/#-defined aperture. Frequencies corresponding to the Nyquist resolution limit of pixel sizes are indicated.




Figure 8: Polychromatic diffraction through-focus MTF at 20 linepairs/mm (image space). Contrast is plotted to two times the focus distance. Note object spatial frequency changes with working distance.

Plots represent theoretical values from lens design software. Actual lens performance varies due to manufacturing tolerances.