



NOTES:

- 1. MATERIAL:  
HOUSING: BLACK ANODIZED ALUMINUM  
LENS: BLACK DIAMOND BD-6
- 2. COATING (APPLY ACROSS COATING APERTURE)  
BBAR (8000 - 12000nm)  
R(AVG) < 0.75% @ 8000 - 12000nm

3. CLEAR APERTURE: 5.11mm

4. RoHS: COMPLIANT



SECTION A-A

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

**Edmund Optics®**

|                        |    |        |                                                                       |                 |
|------------------------|----|--------|-----------------------------------------------------------------------|-----------------|
| THIRD ANGLE PROJECTION |    | TITLE  | LIGHTPATH 7100306   6.3mm FL, f/1.3,<br>THERMAL IMAGING LENS ASSEMBLY |                 |
| ALL DIMS IN            | mm | DWG NO | 15687                                                                 | SHEET<br>1 OF 1 |