

NOTES:

- 1. SUBSTRATE: UV GRADE FUSED SILICA
- 2. COATING (APPLY ACROSS COATING APERTURE): \$1 & \$2: YAG-BBAR (500 - 1100nm) R(ABS) < 0.25% @ 532nm @ 0° AOI R(ABS) < 0.25% @ 1064nm @ 0° AOI R(AVG) < 1.0% FROM 500-1100nm @ 0° AOI
- 3. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN <5 ARCSEC

4. FINE GRIND SURFACE

5. ROHS COMPLIANT





FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2	Edmund Optics®				
SHAPE	PLANO	PLANO	THIRD ANGLE PROJECTION		TITLE	25mm Dia., 1mm Thick, YAG-BBAR Coated λ/10 Fused Silica Window	
SURFACE QUALITY	20-10	20-10					
CLEAR APERTURE	Ø20.00	Ø20.00					
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED	ALL DIMS IN	mm	DWG NO	13353	SHEET 1 OF 1