## NOTES:

- 1. SUBSTRATE: FUSED SILICA
- 2. SURFACE S2 TO BE PARALLEL TO SURFACE S1 TO WITHIN < 5 ARCSEC
- COATING (APPLY ACROSS COATING APERTURE): S1 & S2: R(ABS) ≤ 1.5% FROM 750-800nm @ 0° AOI R(ABS) ≤ 1.0% FROM 800-1550nm @ 0° AOI R(AVG) ≤ 0.7% FROM 750-1550nm @ 0° AOI
- 5. ROHS COMPLIANT

