

NOTES:


- 1. SUBSTRATE: FUSED SILICA (CORNING 7980)
- 2. S2 TO BE PARALLEL WITH S1 TO WITHIN <1 ARCMIN
- 3. COATING (APPLY ACROSS CLEAR APERTURE) \$1 & \$2: R(AVG) ≤0.5% @ 600 - 1050nm

4. FINE GRIND SURFACE

5. ROHS COMPLIANT







FOR INFORMATION ONLY: DO NOT MANUFACTURE PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

	\$1	\$2
SHAPE	PLANO	PLANO
SURFACE QUALITY	40-20	40-20
CLEAR APERTURE (mm)	Ø4.50	Ø4.50
BEVEL	PROTECTIVE AS NEEDED	PROTECTIVE AS NEEDED

			G	Edmund Option	;S®
THIRD ANGLE PROJECTION		TITLE	5mm Dia., 1mm Thick, NIR I Coated, λ/4 Fused Silica Window		
)	ALL DIMS IN	mm	DWG NO	18333	SHEET 1 OF 1