
## NOTES:


- 1. SUBSTRATE: Float Glass
- 2. COATING (APPLY ACROSS CLEAR APERTURE)

S1: Dielectric, ±5% R/T @ 550nm S2: AR 1/4 WAVE MgF2 @ 550nm



4. ROHS COMPLIANT





## FOR INFORMATION ONLY: PARTS TO THIS DRAWING

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY

> SHEET 1 OF 1

	\$1	\$2		
SHAPE	PLANO	PLANO		
SURFACE QUALITY	80-50	80-50		
SURFACE FLATNESS	4 - 6λ	4 - 6λ		
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED		

			Edmund Optics®	
THIRD ANGLE _ PROJECTION	$\phi$	TITLE	25 x 25mm, 25R/75T, AR Coated Plate Beamsplitter	
ALL DIMS IN	mm	DWG NO	13402	SHEET