


- NOTES:
- 1. SUBSTRATE:  
SCHOTT KG3
  - 2. COATING (APPLY ACROSS CLEAR APERTURE)
- S1 & S2: NONE

3. FINE GRIND SURFACE

4. DENSITY (g/cm³): 2.52  
OPERATING TEMPERATURE (°C): 300 Maximum  
REFLECTION FACTOR: 0.92

5. ROHS COMPLIANT



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

**Edmund Optics®**

	S1	S2	THIRD ANGLE PROJECTION		TITLE	SCHOTT KG3, 50mm Dia., 1mm Thick, Colored Glass Heat Absorbing Shortpass Filter	
SHAPE	PLANO	PLANO					
SURFACE QUALITY	60-40	60-40	ALL DIMS IN	mm	DWG NO	19345	SHEET 1 OF 1
BEVEL	PROTECTED AS NEEDED	PROTECTED AS NEEDED					