





NOTES:

1. SUBSTRATE: Hoya L38



LONGPASS FILTER



**FOR INFORMATION ONLY:  
DO NOT MANUFACTURE  
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE  
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
$\Delta\lambda$	<35
TH (%)	>85
CUT-ON WAVELENGTH (nm)	380±5
SURFACE QUALITY	60-40
WAVELENGTH	UV
BEVEL	PROTECTIVE AS NEEDED

 **Edmund Optics®**



ALL DIMS IN

mm

TITLE

Hoya L38 (380nm), 50mm Dia., 2.5mm Thick,  
Colored Glass Longpass Filter

DWG NO

18836

SHEET  
1 OF 1