





NOTES:

- SUBSTRATE: COLORED GLASS




LONGPASS FILTER

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
$\Delta\lambda$	<25
TH (%)	>85
CUT-ON WAVELENGTH (nm)	480 \pm 5
SURFACE QUALITY	60-40
WAVELENGTH	VIS
BEVEL	PROTECTIVE AS NEEDED

THIRD ANGLE
PROJECTION



ALL DIMS IN

mm



Edmund Optics®

TITLE

Hoya Y48 (480nm), 25.4mm Dia., 2.5mm Thick,
Colored Glass Longpass Filter

DWG NO

18866

SHEET
1 OF 1