





NOTES:

- SUBSTRATE: COLORED GLASS




LONGPASS FILTER

**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

| | VALUE |
|------------------------|----------------------|
| SHAPE | PLANO |
| $\Delta\lambda$ | <60 |
| TH (%) | N/A |
| CUT-ON WAVELENGTH (nm) | 850 ± 10 |
| SURFACE QUALITY | 60-40 |
| WAVELENGTH | IR |
| BEVEL | PROTECTIVE AS NEEDED |

THIRD ANGLE
PROJECTION



ALL DIMS IN

mm



Edmund Optics®

TITLE

Hoya IR85N (850nm), 25.4mm Dia., 2.5mm
Thick, Colored Glass Longpass Filter

DWG NO

18906

SHEET
1 OF 1