





NOTES:

- SUBSTRATE: Hoya RM100



LONGPASS FILTER




**FOR INFORMATION ONLY:
DO NOT MANUFACTURE
PARTS TO THIS DRAWING**

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
DIMENSIONS ARE FOR REFERENCE ONLY

	VALUE
SHAPE	PLANO
$\Delta\lambda$	N/A
TH (%)	N/A
CUT-ON WAVELENGTH (nm)	1000
SURFACE QUALITY	60-40
WAVELENGTH	IR
BEVEL	PROTECTIVE AS NEEDED

THIRD ANGLE
PROJECTION



ALL DIMS IN

mm



Edmund Optics®

TITLE

Hoya RM100 (1000nm), 50mm Dia., 2.5mm
Thick, Colored Glass Longpass Filter

DWG NO

18916

SHEET
1 OF 1