NOTES:

1. SUBSTRATE:

TAC FILM


2. COATING (APPLY ACROSS CLEAR APERTURE)

S1 & S2: NONE

3. PROTECTIVE FILM ON BOTH SURFACES SHOULD BE REMOVED BEFORE USE

4. WAVELENGTH RANGE: 300 - 1100 nm

5. ROHS COMPLIANT





SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE DIMENSIONS ARE FOR REFERENCE ONLY



THIRD ANGLE PROJECTION		TITLE	200 x 200mm Light Diffusing Film	
ALL DIMS IN	mm	DWG NO	20220	SHEET 1 OF 1